


SINGLE DUCT TERMINAL UNIT WITH HOT WATER REHEAT AND DISSIPATIVE SILENCER **HOSPITAL GRADE • SUPER QUIET**

OVERSIZED CASING (LARGER WATER COIL) DIGITAL CONTROLS • VARIABLE OR CONSTANT VOLUME **MODEL: D30HQW**

☐ Hot Water Coil Position: Box/Coil/Silencer



Dimensional Data

Unit	Inlet	Airflow Range*	w	Н	Inlet Size	Coil Connections			
Size	Size	cfm (I/s)	VV	п	(Nominal)	1 Row	2 Row	3 Row	4 Row
8	4	0 - 225 (0 - 106)	12 (305)	12 1/2 (318)	3 7/8 (98) Round	1/2 (13)	7/8 (22)	7/8 (22)	7/8 (22)
	5	0 - 400 (0 - 189)			4 7/8 (124) Round	1/2 (13)	7/8 (22)	7/8 (22)	7/8 (22)
	6	0 - 550 (0 - 260)			5 7/8 (149) Round	1/2 (13)	7/8 (22)	7/8 (22)	7/8 (22)
10	7	0 - 800 (0 - 378)	14 (356)	12 1/2 (318)	6 7/8 (175) Round	1/2 (13)	7/8 (22)	7/8 (22)	7/8 (22)
	8	0 - 1100 (0 - 519)			7 7/8 (200) Round	1/2 (13)	7/8 (22)	7/8 (22)	7/8 (22)
12	9	0 - 1400 (0 - 661)	18 (457)	12 1/2 (318)	8 7/8 (225) Round	1/2 (13)	7/8 (22)	7/8 (22)	7/8 (22)
	10	0 - 1840 (0 - 868)			9 7/8 (251) Round	1/2 (13)	7/8 (22)	7/8 (22)	7/8 (22)
14	12	0 - 2500 (0 - 1180)	24 (610)	12 1/2 (318)	12 15/16 x 9 13/16 (329 x 249) Oval	1/2 (13)	7/8 (22)	7/8 (22)	7/8 (22)
16	14	0 – 3125 (0 – 1475)	28 (711)	12 1/2 (318)	16 1/16 x 9 13/16 (408 x 249) Oval	7/8 (22)	7/8 (22)	7/8 (22)	7/8 (22)
24	16	0 - 3725 (0 - 1758)	38 (965)	18 (457)	19 3/16 x 9 13/16 (487 x 249) Oval	7/8 (22)	7/8 (22)	1 3/8 (35)	1 3/8 (35)



* Maximum airflow limit is based upon 1.5" w.g. (373 Pa) max. differential pressure signal from Flow Senso

Standard Features:

- Designed for hospital and other critical environment applications where IAQ is a concern.
- · 22 ga. (0.86) zinc coated steel casing, mechanically sealed. low leakage construction.
- 16 ga. (1.63) corrosion-resistant steel inclined opposed blade damper with extruded PVC seals (single blade on size 4, 5, 6). 45° rotation, CW to close. Tight closeoff. Damper leakage is less than 2% of the terminal rated airflow at 3" w.g. (750 Pa).
- •1/2" (13) dia. plated steel drive shaft. An indicator mark on the end of the shaft shows damper position.
- · Multi-point averaging Diamond Flow Sensor. Supplied with balancing tees.
- · Rectangular discharge with slip and drive cleat duct connection.
- · Full NEMA 1 type controls enclosure for factory mounted controls.
- · VAV section is lined with 13/16" (21), thick, 4 lb. density Steri-Liner insulation. Fiberglass with a reinforced aluminum FSK facing. Meets the requirements of NFPA 90A. UL 181 and ASTM C655.
- "Notch and tuck" fabrication and full seam length steel Z-strip construction.

COUEDINE TYPE.

· Right-hand controls location is standard (shown) when looking in direction of airflow. Optional left hand controls mounting is available.

Silencer Section:

- · Designed to mate with VAV section for optimum performance and super quiet operation.
- · Optimized internal baffle geometry reduces self-generated noise, minimizes pressure drop and maximizes acoustic attenuation.
- · 22 ga. (0.86) coated steel perforated baffles encapsulate fiberglass acoustic media. Mylar lining with acoustical spacer isolates material from airstream.
- · Internal Steri-Liner insulation on top and bottom optimizes sound reduction and eliminates need for external field applied thermal duct wrap.

Hot Water Coil Section:

- · Position: Box/Coil/Silencer (shown above).
- 1/2" (13) Copper tubes and aluminum ripple fins, 10 per inch.
- · 20 ga. (1.00) zinc coated steel casing. Uninsulated.
- · Left or right hand connection. Determined by looking in direction of airflow (RH illustrated).

SS	
Listed	



• 1/2" (13), 7/8" (22) or 1 3/8" (35) O.D. male solder sweat connections.

Diaital	Control	
Diuliai	COILLO	.

- ☐ Factory mounted (supplied by others)
- ☐ Field mounted (supplied by others)
- Nailor EZvav

See separate submittal.

Options and Accessories:

- ☐ Solid metal liner (VAV section).
- ☐ HW coil position: Box/Silencer/Coil (see page 2).
- Access door.
- 2 Access doors.
- ☐ Removable insert type Flow Sensor.
- ☐ 20 ga. (1.00) construction.
- 24 VAC control transformer.
- Toggle disconnect switch.
- Hanger brackets.
- Controls enclosure for field mounted controls.
- ☐ Dust tight enclosure seal.

Seismic Certification:

- ☐ Seismic Source International (Standard)
- ☐ HCAI (formerly OSHPD, California)
- Special Features:


SCHEDULE TIPE.	Page 1 of 2.			
PROJECT:	Dimensions are in inches (mm)			
ENGINEER:	DATE	B SERIES	SUPERSEDES	DRAWING NO
CONTRACTOR:	4 - 3 - 23	3000	4 - 11 - 22	D30HQW-0



SINGLE DUCT TERMINAL UNIT WITH HOT WATER REHEAT AND DISSIPATIVE SILENCER HOSPITAL GRADE • SUPER QUIET

OVERSIZED CASING (LARGER WATER COIL)
DIGITAL CONTROLS • VARIABLE OR CONSTANT VOLUME
MODEL: D30HQW

☐ Hot Water Coil Position: Box/Silencer/Coil



SCHEDULE TYPE:	Page 2 of 2.			
PROJECT:	Dimensions are in inches (mm)			
ENGINEER:	DATE	B SERIES	SUPERSEDES	DRAWING NO.
CONTRACTOR:	4 - 3 - 23	3000	4 - 11 - 22	D30HQW-OC