

PERFORMANCE DATA:

Model 4310A • 24 x 24 (600 x 600) Module Size

Nominal Neck Size	Neck Velocity, FPM	300	400	500	600	700	800	900	1000	1200	1400
	Velocity Pressure	.006	.010	.016	.023	.031	.040	.051	.063	.090	.122
6" Dia.	Total Pressure	.005	.008	.013	.016	.025	.032	.041	.050	.072	.098
	Airflow, CFM	60	80	100	120	140	160	180	195	235	275
	Throw	1-1-2	1-1-2	1-1-3	1-2-3	1-2-4	1-2-4	2-3-5	2-3-6	2-3-7	3-4-8
	Noise Criteria	—	—	16	18	20	22	24	26	31	37
8" Dia.	Total Pressure	.009	.015	.024	.034	.046	.061	.077	.095	.136	.185
	Airflow, CFM	105	140	175	210	245	280	315	350	420	490
	Throw	1-1-3	1-2-3	1-2-4	2-3-5	2-3-6	2-3-7	3-4-8	3-4-9	3-5-10	4-6-12
	Noise Criteria	—	—	18	21	24	27	31	34	39	46
10" Dia.	Total Pressure	.013	.023	.037	.053	.072	.094	.119	.147	.211	.288
	Airflow, CFM	165	220	270	325	380	435	490	585	655	765
	Throw	1-2-4	2-2-5	2-3-6	2-4-7	3-4-8	3-5-10	4-5-11	4-6-12	5-7-14	6-8-17
	Noise Criteria	—	—	19	22	25	28	33	36	41	48
12" Dia.	Total Pressure	.016	.031	.049	.070	.095	.125	.158	.195	.260	.382
	Airflow, CFM	235	315	390	470	550	630	705	785	940	1100
	Throw	2-2-5	2-3-6	3-4-8	3-5-9	4-5-11	4-6-12	5-7-14	6-8-15	6-9-18	7-11-21
	Noise Criteria	—	16	21	25	29	32	35	38	44	50
14" Dia.	Total Pressure	.021	.038	.059	.085	.115	.151	.191	.235	.339	.461
	Airflow, CFM	320	430	535	640	750	855	960	1070	1285	1495
	Throw	2-3-5	2-4-7	3-5-9	4-5-11	4-6-13	5-7-14	5-8-16	6-9-18	7-11-22	8-13-25
	Noise Criteria	—	16	22	27	32	35	39	43	49	53
15" Dia.	Total Pressure	.022	.040	.062	.090	.122	.160	.202	.250	.359	.489
	Airflow, CFM	370	490	615	735	860	980	1105	1230	1475	1720
	Throw	2-3-5	3-4-7	3-5-10	4-6-11	5-7-13	5-8-15	6-9-17	7-10-19	8-12-23	9-14-27
	Noise Criteria	—	17	23	29	34	37	41	45	51	55

Performance Notes:

1. All pressures are in inches w.g.. To obtain static pressure, subtract the velocity pressure from the total pressure.
2. Throws are given at 150, 100 and 50 fpm terminal velocities, under isothermal conditions.

3. Noise Criteria (NC) values are based upon 10 dB room absorption, re 10⁻¹² watts. Dash (—) in space indicates an Noise Criteria of less than 15.

4. Data derived from tests conducted in accordance with ANSI/ASHRAE Standard 70 – 2025.

Balancing:

It is recommended that a commercially available 'Flow Hood' is used for field balancing. The airflow meter directly reads average flow rate with great accuracy at all volumes. It is a much faster and more accurate alternative to time consuming multiple velocity readings, eliminating the use of Ak factors and the calculations required to convert the average velocity into airflow.