

PERFORMANCE DATA:

Models 4320MR, 4320MRA, 4325MR, 4325MRA • 12 x 12 (300 x 300) Module Size • Round Neck

Nominal Neck Size	Neck Velocity, FPM	300	400	500	600	700	800	1000
	Velocity Pressure	.006	.010	.016	.023	.031	.040	.063
6" Dia.	Total Pressure	.016	.031	.041	.065	.092	.124	.163
	Flow Rate, CFM	60	80	100	115	135	155	195
	Throw 4-Way	1-1-1	1-1-2	1-1-3	1-1-4	1-2-5	1-2-5	2-3-7
	3-Way	1-1-3	1-2-5	2-3-6	2-3-7	3-4-8	3-5-9	4-6-12
	2-Way	1-1-3	1-1-4	1-2-5	1-3-6	1-4-8	2-4-9	3-5-11
	1-Way	1-1-4	1-1-7	1-2-8	1-4-9	2-5-10	3-7-13	5-8-15
8" Dia.	Noise Criteria	—	—	18	23	29	33	38
	Total Pressure	.015	.027	.043	.062	.084	.110	.171
	Flow Rate, CFM	105	140	175	210	245	280	350
	Throw 4-Way	1-1-2	1-1-4	1-2-5	1-2-6	1-3-7	2-4-8	3-5-10
	3-Way	1-2-5	1-3-7	2-4-8	3-5-9	4-6-11	4-7-13	5-9-16
	2-Way	1-1-4	1-2-6	1-3-9	2-4-9	3-5-11	3-6-13	5-8-16
8" Dia.	1-Way	1-2-7	1-4-9	2-6-12	4-7-14	5-9-17	6-10-19	8-13-21
	Noise Criteria	—	15	24	27	33	37	42

Performance Notes:

1. All pressures are in inches w.g..
2. Throws are given at 150, 100 and 50 fpm terminal velocities under isothermal conditions.
3. Noise Criteria (NC) values are based upon 10 dB room absorption, re 10⁻¹² watts. Dash (—) in space indicates an Noise Criteria of less than 10.

4. Data derived from tests conducted in accordance with ANSI/ASHRAE Standard 70 – 2025.

Balancing:

It is recommended that a commercially available 'Flow Hood' is used for field balancing. The airflow meter directly reads average flow rate with great accuracy at all volumes. It is a much faster and more accurate alternative to time consuming multiple velocity readings, eliminating the use of Ak factors and the calculations required to convert the average velocity into airflow.