

PERFORMANCE DATA:

Models 4320M, 4320MA, 4325M, 4325MA • 12 x 12 (300 x 300) Module Size • Square Neck

Nominal Neck Size	Neck Velocity, FPM	300	400	500	600	700	800	900	
	Velocity Pressure	.006	.010	.016	.023	.031	.040	.051	
6 x 6	Total Pressure	.030	.048	.071	.119	.155	.196	.244	
	Flow Rate, CFM	75	100	125	150	175	200	225	
	Throw	4-Way	1-1-2	1-1-3	1-2-4	1-2-5	2-3-6	2-3-6	2-4-7
		3-Way	1-2-4	2-3-6	2-4-8	3-4-9	3-5-10	4-6-11	4-7-11
		2-Way	2-3-6	2-4-8	3-5-10	4-6-12	4-7-13	5-8-14	6-9-15
1-Way		3-4-9	4-6-12	5-8-16	6-9-19	7-11-20	8-12-22	9-14-22	
Noise Criteria	—	—	19	24	30	34	39		
8 x 8	Total Pressure	.028	.042	.064	.110	.141	.186	.240	
	Flow Rate, CFM	135	175	220	265	310	355	400	
	Throw	4-Way	1-1-3	1-2-5	2-3-6	2-3-7	2-4-8	3-5-8	3-5-9
		3-Way	2-3-6	2-4-8	3-5-10	4-6-13	5-7-14	5-8-15	6-9-15
		2-Way	2-4-8	3-5-11	4-6-13	5-8-16	6-9-18	7-11-19	8-12-20
1-Way		4-6-12	5-8-17	7-10-21	8-12-25	10-15-27	11-17-29	12-19-31	
Noise Criteria	—	16	23	28	34	38	43		

Performance Notes:

1. All pressures are in inches w.g..
2. Throws are given at 150, 100 and 50 fpm terminal velocities under isothermal conditions.
3. Noise Criteria (NC) values are based upon 10 dB room absorption, re 10⁻¹² watts. Dash (—) in space indicates an Noise Criteria of less than 15.

4. Data derived from tests conducted in accordance with ANSI/ASHRAE Standard 70 – 2006.

Balancing:

It is recommended that a commercially available 'Flow Hood' is used for field balancing. The airflow meter directly reads average flow rate with great accuracy at all volumes. It is a much faster and more accurate alternative to time consuming multiple velocity readings, eliminating the use of Ak factors and the calculations required to convert the average velocity into airflow.

PERFORMANCE DATA:

Models 4320M, 4320MA, 4325M, 4325MA • 24 x 24 (600 x 600) Module Size • Square Neck

Nominal Neck Size	Neck Velocity, FPM		300	400	500	600	700	800	900
	VP		.006	.010	.016	.023	.031	.040	.051
6 x 6	Total Pressure		.024	.042	.065	.098	.130	.169	.202
	Flow Rate, CFM		75	100	125	150	175	200	225
	Throw	4-Way	1-1-2	1-1-3	1-2-4	1-2-5	2-3-6	2-3-6	2-4-7
		3-Way	1-2-4	2-3-6	2-4-8	3-4-9	3-5-10	4-6-11	4-7-11
		2-Way	2-3-6	2-4-8	3-5-10	4-6-12	4-7-13	5-8-14	6-9-15
1-Way		3-4-9	4-6-12	5-8-16	6-9-19	7-11-20	8-12-22	9-14-22	
Noise Criteria		—	—	15	19	23	29	31	
8 x 8	Total Pressure		.024	.042	.065	.098	.130	.169	.202
	Flow Rate, CFM		135	175	220	265	310	355	400
	Throw	4-Way	1-1-3	1-2-5	2-3-6	2-3-7	2-4-8	3-5-8	3-5-9
		3-Way	2-3-6	2-4-8	3-5-10	4-6-13	5-7-14	5-8-15	6-9-15
		2-Way	2-4-8	3-5-11	4-6-13	5-8-16	6-9-18	7-11-19	8-12-20
1-Way		4-6-12	5-8-17	7-10-21	8-12-25	10-15-27	11-17-29	12-19-31	
Noise Criteria		—	—	18	23	27	33	35	
10 x 10	Total Pressure		.034	.050	.073	.124	.160	.226	.263
	Flow Rate, CFM		210	275	345	415	485	555	625
	Throw	4-Way	1-2-4	2-3-6	2-3-7	3-4-9	3-5-10	4-6-11	4-7-11
		3-Way	2-4-8	3-5-10	4-6-13	5-8-16	6-9-17	7-10-18	8-12-19
		2-Way	3-5-10	4-6-13	5-8-17	6-10-20	8-12-22	9-13-24	10-15-25
1-Way		5-8-16	7-10-21	8-13-26	10-16-32	12-18-34	14-21-37	16-24-39	
Noise Criteria		—	—	21	26	30	36	38	
12 x 12	Total Pressure		.036	.052	.085	.127	.169	.230	.276
	Flow Rate, CFM		300	400	500	600	700	800	900
	Throw	4-Way	1-2-5	2-3-7	3-4-9	3-5-11	4-6-12	5-7-13	5-8-14
		3-Way	3-4-9	4-6-13	5-8-16	6-9-19	7-11-21	8-13-22	9-14-23
		2-Way	4-6-12	5-8-16	6-10-20	8-12-25	9-14-27	11-16-28	12-18-30
1-Way		6-9-19	8-12-25	10-16-32	12-19-38	15-22-41	17-25-44	19-29-47	
Noise Criteria		—	—	25	30	34	39	42	
15 x 15	Total Pressure		.039	.058	.096	.129	.177	.236	.291
	Flow Rate, CFM		470	625	780	935	1095	1250	1405
	Throw	4-Way	2-3-7	3-4-9	4-6-12	4-7-14	5-8-15	6-9-16	7-10-17
		3-Way	4-6-12	5-8-16	6-10-20	8-12-24	9-14-26	10-16-28	12-18-29
		2-Way	5-7-15	6-10-20	8-13-26	10-15-31	12-18-33	13-20-36	15-23-38
1-Way		8-12-24	10-16-32	13-20-40	16-24-48	18-28-52	21-32-56	24-36-59	
Noise Criteria		—	19	28	33	37	42	45	
18 x 18	Total Pressure		.041	.062	.110	.135	.186	.240	.301
	Flow Rate, CFM		675	900	1125	1350	1575	1800	2025
	Throw	4-Way	2-4-8	3-5-11	4-7-14	5-8-17	6-10-18	7-11-19	8-12-21
		3-Way	4-7-14	6-9-19	8-12-24	9-14-29	11-17-31	13-19-33	14-22-35
		2-Way	6-9-18	8-12-25	10-15-31	12-18-37	14-21-40	16-25-43	18-28-46
1-Way		9-14-29	12-19-38	16-24-48	19-29-58	24-34-62	25-38-67	29-43-71	
Noise Criteria		—	22	31	36	41	46	49	

Performance Notes:

1. All pressures are in inches w.g..
2. Throws are given at 150, 100 and 50 fpm terminal velocities under isothermal conditions.
3. Noise Criteria (NC) values are based upon 10 dB room absorption, re 10⁻¹² watts. Dash (—) in space indicates an Noise Criteria of less than 15.

4. Data derived from tests conducted in accordance with ANSI/ASHRAE Standard 70 – 2006.

Balancing:

It is recommended that a commercially available 'Flow Hood' is used for field balancing. The airflow meter directly reads average flow rate with great accuracy at all volumes. It is a much faster and more accurate alternative to time consuming multiple velocity readings, eliminating the use of Ak factors and the calculations required to convert the average velocity into airflow.

D
CEILING DIFFUSERS