

PERFORMANCE DATA:

Models 4340CB, 4340CBA • Surface Mount • Square Neck

Nominal Neck Size	Neck Velocity, FPM		200	300	400	500	600	700	800	900
	Velocity Pressure		.003	.006	.010	.016	.022	.031	.040	.050
	Total Pressure		.014	.032	.057	.089	.129	.175	.229	.290
6 x 6	Flow Rate, CFM		50	75	100	125	150	175	200	225
	Throw	4-Way	1-1-3	2-3-4	3-4-5	3-5-6	4-5-7	4-6-8	5-7-9	6-8-10
		3-Way	1-2-3	2-3-4	3-5-6	4-5-7	5-7-9	6-8-10	6-9-12	7-10-13
		2-Way	2-3-4	3-4-5	4-5-7	5-7-9	6-9-12	7-10-13	8-12-15	8-12-16
		1-Way	3-4-5	4-5-7	5-7-9	6-8-11	7-11-14	8-12-16	9-14-18	11-16-21
	Noise Criteria		—	21	25	28	31	34	36	38
8 x 8	Flow Rate, CFM		89	133	176	222	267	311	356	400
	Throw	4-Way	2-3-4	3-4-5	3-5-6	4-5-7	4-6-8	5-7-9	5-7-10	6-9-12
		3-Way	2-3-4	3-4-5	4-5-7	4-6-8	5-7-10	6-9-12	7-10-13	7-11-14
		2-Way	3-4-5	3-5-6	4-6-8	5-7-10	7-10-13	7-11-14	8-12-16	9-14-18
		1-Way	3-5-6	4-6-8	5-7-10	6-9-12	8-12-15	9-13-17	10-15-19	11-16-22
	Noise Criteria		—	23	27	30	33	35	37	39
10 x 10	Flow Rate, CFM		139	208	278	347	417	486	556	625
	Throw	4-Way	2-3-4	3-5-6	4-6-8	6-8-11	6-9-12	7-11-14	8-12-16	9-14-18
		3-Way	3-5-6	4-6-8	5-7-10	7-10-13	8-12-15	9-14-18	10-15-20	11-16-22
		2-Way	4-6-8	6-8-11	7-10-13	8-12-16	10-15-20	12-17-23	13-19-26	15-20-23
		1-Way	5-7-9	6-9-12	8-12-16	10-15-20	12-18-24	14-21-28	16-24-32	18-27-36
	Noise Criteria		—	23	28	31	34	36	38	40
12 x 12	Flow Rate, CFM		200	300	400	500	600	700	800	900
	Throw	4-Way	3-5-6	4-6-8	5-7-10	6-9-12	8-12-15	9-13-17	10-15-20	12-17-23
		3-Way	3-5-6	5-7-9	6-9-12	8-12-15	9-14-18	11-16-22	13-19-25	14-20-27
		2-Way	5-7-9	6-9-12	8-12-16	11-16-21	12-18-24	15-22-29	17-25-33	18-27-36
		1-Way	6-9-12	8-12-16	10-15-20	12-18-24	15-22-29	17-25-33	18-27-36	21-31-42
	Noise Criteria		—	23	27	31	34	36	39	41
14 x 14	Flow Rate, CFM		272	408	544	681	817	953	1089	1225
	Throw	4-Way	4-5-7	4-6-9	6-9-12	7-11-14	9-14-18	10-15-20	12-18-24	14-21-28
		3-Way	4-5-9	5-8-11	6-10-13	8-13-16	10-15-20	11-17-23	13-19-27	16-23-31
		2-Way	5-7-10	6-9-13	8-12-18	11-17-22	12-19-26	16-23-31	18-26-36	19-29-39
		1-Way	6-9-12	8-12-18	10-15-22	13-19-26	15-23-30	17-25-35	19-28-39	21-31-43
	Noise Criteria		—	24	28	32	35	37	40	42
16 x 16	Flow Rate, CFM		355	533	711	889	1067	1244	1422	1600
	Throw	4-Way	5-7-9	6-8-11	8-10-14	9-13-18	10-15-21	13-18-27	14-20-28	16-22-31
		3-Way	5-7-11	6-9-13	8-13-17	10-15-22	13-19-26	15-22-30	18-25-36	19-29-39
		2-Way	6-10-12	9-14-16	11-17-24	14-21-28	17-25-32	19-26-34	21-34-40	24-34-44
		1-Way	7-10-16	9-15-18	12-18-26	15-22-32	18-27-36	19-28-37	24-35-42	26-36-46
	Noise Criteria		—	27	31	35	37	40	42	44
18 x 18	Flow Rate, CFM		450	675	900	1125	1350	1575	1800	2025
	Throw	4-Way	5-7-10	6-9-12	8-12-16	10-15-20	12-18-24	14-21-28	16-24-32	18-27-36
		3-Way	5-7-12	7-11-14	9-14-18	11-16-22	13-19-26	16-24-31	18-27-36	21-31-41
		2-Way	8-12-18	10-15-20	13-19-26	16-24-32	20-29-39	23-34-45	26-39-52	29-43-58
		1-Way	9-14-22	11-16-24	15-23-30	18-27-36	22-32-43	25-37-49	28-42-56	30-45-60
	Noise Criteria		—	28	32	36	38	41	43	45

Performance Notes:

1. All pressures are in inches w.g..
2. Throws are given at 150, 100 and 50 fpm terminal velocities under isothermal conditions.
3. Noise Criteria (NC) values are based upon 10 dB room absorption, re 10⁻¹² watts. Dash (—) in space indicates an Noise Criteria of less than 20.

4. Data derived from tests conducted in accordance with ANSI/ASHRAE Standard 70 – 2023.

Balancing:

It is recommended that a commercially available 'Flow Hood' is used for field balancing. The airflow meter directly reads average flow rate with great accuracy at all volumes. It is a much faster and more accurate alternative to time consuming multiple velocity readings, eliminating the use of Ak factors and the calculations required to convert the average velocity into airflow.