
Recommended Airflow Ranges For Model 36VRR Round Retrofit Terminal Units

The recommended airflow ranges below are for Round Duct Retrofit Terminal Units with pressure independent controls and are presented as ranges for total and controller specific minimum and maximum airflow. Airflow ranges are based upon maintaining reasonable sound levels and controller limits using Nailor's Diamond Flow Sensor as the airflow measuring device. For a given unit size, the minimum, auxiliary minimum (where applicable) and the maximum flow setting must be within the range limits to ensure pressure independent operation, accuracy and repeatability.

Minimum airflow limits are based upon .02" w.g. (5 Pa) differential pressure signal from Diamond Flow Sensor on analog/digital controls and .03" (7.5) for pneumatic controllers. This is a realistic low limit for many transducers used in the digital controls industry. Check with your controls supplier for minimum limits. Setting airflow minimums lower, may cause hunting and failure to meet minimum ventilation requirements. Factory settings will therefore not be made outside these ranges. A minimum setting of zero (shut-off) is also available. Where an auxiliary setting is specified, the value must be greater than the minimum setting.

The high end of the tabulated Total Airflow Range on pneumatic and analog electronic controls represents the Diamond Flow Sensor's differential pressure reading at 1" w.g. (250 Pa). The high end airflow range for digital controls is represented by the indicated transducer differential pressure.



ASHRAE 130 "Performance Rating of Air Terminals" is the method of test for the certification program. The "standard rating condition" (certification rating point) airflow volumes for each terminal unit primary valve size are tabulated below per AHRI Standard 880. These air volumes equate to an approximate inlet velocity of 2000 fpm (10.2 m/s).

When digital or other controls are mounted by Nailor, but supplied by others, these values are guidelines only, based upon experience with the majority of controls currently available. Controls supplied by others for factory mounting are configured and calibrated in the field. Airflow settings on pneumatic and analog controls supplied by Nailor are factory preset when provided.

Imperial Units, Cubic Feet per Minute

	Inlet Type	Total Airflow Range,	low Inlet ige, Velocity	Range of Minimum and Maximum Settings, cfm								
Unit Size				Pneumatic 3000 Controller		Analog Electronic Controls		Digital Controls				
				Transducer Differential Pressure ("w.g.)								
		cfm		Min.	Max.	Min.	Max.	Min.	Max.			
			(110111.), 0111	.03	1.0	.02	1.0	.02	1.0	1.25	1.5	
4	Round	0 – 225	150	30	180	25	180	25	180	200	225	
5		0 - 400	250	55	325	45	325	45	325	350	400	
6		0 – 550	400	80	450	65	450	65	450	500	550	
7		0 - 800	550	115	650	95	650	95	650	725	800	
8		0 – 1100	700	155	900	125	900	125	900	1000	1100	
9		0 - 1400	900	200	1150	165	1150	165	1150	1285	1400	
10		0 - 1840	1100	260	1500	215	1500	215	1500	1675	1840	
12		0 - 2500	1600	350	2050	290	2050	290	2050	2290	2500	
14		0 – 3370	2100	475	2750	390	2750	390	2750	3075	3370	
16		0 – 4525	2800	640	3700	520	3700	520	3700	4140	4525	

Metric Units, Liters per Second

Unit Size	Inlet Type	Total Airflow Range, I/s	Airflow at 10.2 m/s Inlet Velocity (nom.), I/s	Range of Minimum and Maximum Settings, I/s								
				Pneumatic 3000 Controller		Analog Electronic Controls		Digital Controls				
				Transducer Differential Pressure (Pa)								
				Min.	Max.	Min.	Max.	Min. Max.				
				7.5	249	5	249	5	249	311	374	
4	Round	0 – 106	71	14	85	12	85	12	85	94	106	
5		0 – 189	118	26	153	21	153	21	170	165	189	
6		0 – 260	189	38	212	31	212	31	212	236	260	
7		0 – 378	260	54	307	45	307	45	342	307	378	
8		0 – 579	330	73	425	59	425	59	472	425	579	
9		0 - 661	425	94	543	78	543	78	606	495	661	
10		0 - 868	519	123	708	101	708	101	790	637	868	
12		0 – 1081	755	165	967	137	967	137	1081	1015	1081	
14		0 – 1590	991	224	1298	184	1298	184	1451	1444	1590	
16		0 – 2135	1321	302	1746	245	1746	245	1954	1911	2135	

D